ALBÉR CELLCORDER[®] CRT-400 CELL RESISTANCE TESTER

Technology That Lets You Trust Your Batteries

BENEFITS

- Patented Internal Resistance testing eliminates inaccuracy
- New graphical display makes menu navigation easy
- Measures cell voltage and internal battery resistance as well as intercell resistance
- Flash drive can be used to transfer data to your PC Battery Analysis PC software lets you identify bad cells, create reports and archive data
- IrDa allows wireless communication with a variety of peripheral equipment including compatible DMA-35N-CRT Hydrometer
- Tests batteries from 0-16V
- Includes new battery test clamps with interchangeable jaws



CELLCORDER® CRT-400 Cell Resistance Tester

The CELLCORDER® CRT-400 Cell Resistance Tester was specially designed to strictly comply with IEEE standards for testing batteries online. When a battery is tested online, the test is subjected to ripple from the charger, which makes ohmic measurement tests complicated. The well-proven Alber DC resistance test method completely eliminates these distorting factors. The Cellcorder outstrips competitive testing instruments by producing very high repeatability in testing. The Cellcorder comes with easy keyboard entry, hard shell carrying case, AC charger, data trending and analysis software and a user-friendly manual. An optional IR printer is available.



1

The New CELLCORDER® at a glance.

Lightweight, stylish, rugged and durable. Special features include new user friendly operation, Bluetooth, modem, graphical transreflective LCD display for better contrast, and new cables and clamps.



- A. **Ventilation:** Temperature controlled colling fan
- B. Test Lead Connector: Molded test cables and optimized battery clamps
- C. **Bluetooth® Capable:** audible voice status during testing and data transfer to your PC
- D. Shoulder Strap: (not shown) Adjustable shoulder strap for safe and efficient testing
- E. **Keypad:** Combination keypad for alphanumeric data entry. Shift key for quick function keys.
- F. **Test Key:** Initiates the test sequence
- G. **Transreflective LCD:** Backlit graphical LCD display with excellent contrast. Improved contrast in direct sunlight.
- H. **AC Power Indicator:** Illuminated when connected to AC power
- I. Battery Charge Indicator: Indicates battery charging progress
- J. **Multi Function Menu Buttons:** Interactive buttons that correlate to relevant menu alternatives on screen
- K. **Power On/Off:** Press for start-up. Press and hold for shut down
- L. **Navigation Key:** Easily navigate and select choice in menus
- M. **Infrared Port:** (not shown) Wireless IrDA communication to printer, PDA, DMA-35N-CRT Hydrometer or laptop
- N. **Beeper:** Alerts valid entry or faulty test results

The test screen show the cell number,

internal resistance, voltage and four

intercell connections.



(Shown with optional accessories)



The Battery Analysis Software helps you identify bad cells, generate descriptive reports and archive data.

Measurements are stored and presented to allow trending and make it possible to detect early performance degradation in individual battery cells.



The new graphical display makes it easier to navigate through the menus.





Ensuring The High Availability Of Mission-Critical Data And Applications.

| ALBER CELLCORDER CRT-400 SPECIFICATIONS | | |
|---|--|--|
| PHYSICAL | | |
| Dimensions | H 305mm (12") x W 178mm (7") x D 76mm (3") | |
| Weight | 1.5Kg (3.4lb) | |
| Keypad | Rubber keys with polyurethane coat | |
| DISPLAY | | |
| Туре | LCD - STN Reflective | |
| Viewing Area | 2.619" x 1.309" | |
| Resolution | Graphics LCD 128 x 64 | |
| Viewing Angle | 40° | |
| Backlight | White LED | |
| MEMORY | | |
| Туре | USB Flash Drive | |
| Storage Capability 1 MB per 71 strings with 256 cells | | |
| Data retention | 10 years | |

| | · · · · · · · · · · · · · · · · · · · |
|--------------------|---|
| COMMUNICATION | |
| Infrared | PC Interface for data transfer Physical IrDA compliant for printer interface |
| Bluetooth (option) | PC interface for data transfer |

| | Earpiece interface for voice test status | | | |
|-------|--|--|-----------------------|---------------------------------------|
| INPUT | TEST CURRENT | RESISTANCE RESOLUTION ±0.1% OF READING | VOLTAGE RESOLUTION | INTERCELL RANGE/ RESOLUTION |
| 2V | 50A | $\pm 5\mu\Omega$ | 0.1% - ± 1mV | $2m\Omega \pm 2\mu\Omega$ |
| 4-6V | 25-30A | $\pm 25 \mu \Omega$ | 0.1% - ± 3mV | $3.3 \text{m}\Omega \pm 5 \mu \Omega$ |
| 8-12V | 30-35A | $\pm 75 \mu \Omega$ | 0.1% - ± 6mV | $5m\Omega$ ± $10\mu\Omega$ |
| 16V | 5A | ±400μΩ | 0.1%- ± 10mV | $20m\Omega \pm 20\mu\Omega$ |

WARRANTY

1-year limited warranty

ORDERING INFORMATION

| 1000-056 | Cellcorder including software, carrying case, USB Flash drive, battery charger, cables, test and voltage | | | |
|----------------------|--|------------|-----------------------------|--|
| OPTIONAL ACCESSORIES | | OPTIONAL | ACCESSORIES | |
| 1000-056BT | CRT with Bluetooth option | 2120-053 A | JAWS (see www.vertivco.com) | |
| 2025-036 | Bluetooth wireless headset | 2120-056 | JAWS (see www.vertivco.com) | |
| 2025-124 | Printer with IRDA interface | 2120-057 | JAWS (see www.vertivco.com) | |
| Various | Spike probe options | 2120-0581 | JAWS (see www.vertivco.com) | |
| 2030-004 | USB Flash Drive | | | |

*Specifications subject to change without notice.

VertivCo.com | Vertiv Headquarters, 1050 Dearborn Drive, Columbus, OH, 43085, USA

© 2016 Vertiv Co. All rights reserved. Vertiv, the Vertiv logo are trademarks or registered trademarks of Vertiv Co. All other names and logos referred to are trade names, trademarks or registered trademarks of their respective owners. While every precaution has been taken to ensure accuracy and completeness herein, Vertiv Co. assumes no responsibility, and disclaims all liability, for damages resulting from use of this information or for any errors or omissions. Specifications are subject to change without notice.

| Туре | 4 cell - 8800 mAh lithium ion |
|--------------------|--|
| Voltage | 4.2V |
| Charge Time | 8 hrs |
| AC ADAPTER | |
| Input Voltage | 90 - 264 VAC |
| Output Voltage | 5 VDC |
| Output Current | 4.0 Amps |
| Frequency | 47 - 63 HZ |
| ENVIRONMENTAL | |
| Temperature Range: | |
| Operating | 0° - 40°C (32° — 104°F) |
| Storage | -20° - 60°C (-20° — 140°F) For extended periods <25° (<77°F) |
| Humidity Range | 0% to 80% RH (non-condensing) at 0°- 31°C 0% to 50% RH (non-condensing) at 32°- 40°C |
| Pollution Degree 2 | |
| | |

BATTERY

0 to 2000 meters above sea level